

EVIscreen

the modular evidence screening stand

Benefits at a Glance

Comfortable & Safe Operation of Forensic Photography and Screening Systems

Combine the camera system of your choice with a configurable stand that fits your application.

Manually Operated or Motorized Camera Column

A choice of two different camera columns allows manual fast adjustment between close-ups and full images, or the convenience of motorized fine adjustment.

Basic Camera Mount or Segmented Camera Arm

A simple camera mount allows the operation of almost any camera system. Should you need to screen larger pieces of evidence, we recommend selecting the segmented arm that allows the camera to view almost every point on the working surface.

Height Adjustable Working Platform

Platforms, available in two sizes, fixed or adjustable in height, featuring an epoxy or stainless steel working surface complement your screening system.

Downdraft Air Filter System

If your system is fitted with a working platform and you want to avoid inhaling particulate dust or fumes from evidence or developers, add the optional self-contained filtration system, which creates a steady air stream away from the user. If you require the filtration of any specific material, customized filters can be added.


Base Stand

The base stand of **EVIscreen** can be fitted with either levelling feet or with locking casters.

Alternatively, if no working platform is required, the camera column can also come a wall mount setup instead of the base stand.



EVIscreen is the perfect addition to the Attestor **LABview** system



Working Platform and Height Adjustment

EVIscreen can be equipped with a fixed or height adjustable working platform. The surface material comes in two versions: stainless steel or epoxy coated

Two sizes of working platforms are available. The smaller version offers a workspace of 70 x 100 cm. The dimensions of the large model are 75 x 150 cm. The small model (pictured) can be fitted with motorized height adjustment using two synchronised lifters. The large model requires three synchronised lifters and can also be outfitted for motorized height adjustment.

Camera Column

Two different types of camera columns are available with **EVIscreen**. You can select a manually operated column featuring a counter balance for smooth operation, or choose our motorized height adjustable camera column, ideal for camera systems that require fine distance adjustments to focus. This option comes with a cable remote control for ease of use.

Cable management ensures that cables for the camera system and workstation are protected and contained, and move together to ensure no tangling or pulling occurs.

Camera Arm

Both camera columns of **EVIscreen** can be fitted with either a fixed camera mount or a segmented arm (pictured) with an apx.100cm range of motion. The segmented arm is particularly useful when larger items need to be screened for DNA or fibers without moving the evidence.

Downdraft Venting & Filter

If **EVIscreen** is equipped with the stainless steel working platform (height adjustable or fixed), this can further be upgraded with a downdraft filter system.



A self-contained filter system consisting of a two-stage filter (pre-filter mat M5 and a fine particulate dust filter cassette H13) is then mounted directly below the working surface to ensure pollution-free and safe screening of evidence material.

TABLEcol, our table- and bench-mount camera column is also now available.

